


M-3703 3



NOTES:

1. WIRE CAPACITY: #10AWG - #6AWG, SOLID OR STRANDED COPPER WIRE.
2. SUPPLIED WITH (4) #6-32 X .656 MOUNTING SCREWS.
3. ALL DIMENSIONS TO BE INCHES.  
[mm]
4. FOR MOUNTING TO SINGLE GANG "FS" & "FD" BOXES (GROUNDED).

CODE 74545

TITLE  
20A 250VDC 30A 600VAC  
5 WIRE HUBBELLOCK RECEPTACLE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOLDER	BAKELITE	BLACK
BODY	BAKELITE	BLACK
COVER PLATE	CAST ALUM	BLUE SPRAY
GR. SPRING	.031 BRONZE	
CONTACT SPRINGS	.031 BRONZE	
PRESS. TERMINAL	COPPER	
CENTER POST	STEEL	ZINC PL
AUX. SPRING	.020 PHOS BRZ	
COIL SPRING	MU. WIRE	ZINC PL
EYELET	.008 BRASS	
TH'D. SLUG	STEEL	ZINC PL.

SYM	REVISIONS	APP	DATE
3	ADDED NOTES 1 THRU 4; "HBL25403" WAS 25403; CONVERTED ALL DIMS. TO DECIMAL/METRIC; REVISED TITLE PER DCN 11902 RCM	JPP	1/27/05
2	X REMOVED FROM CAT. NO.		4-21-69
1	REDRAWN		11-9-67

SUPERSEDES DWG. DATED 8-18-60

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
		BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY A.J.L.	APP. BY	
DECIMALS ± .005	TR. BY	SCALE FULL	
ANGLES ± 2°	CHK'D. BY ZGL	DATE 11-9-67	

DIMENSION SHEET FOR CAT. NO. HBL25403  
 REPAIRABLE  NON-REPAIRABLE   
 B  
 M-3703  
 3