

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	6/3/2009 12:00:00 AM	REDRAW INTO PRO-E	17968	DG	MA

D	CATALOG NUMBER	BARREL 'A'				BARREL 'B'				DIE INDEX NO.	HYTOOL™ WITH NUMBER OF CRIMPS PER END			HYPRESS™ WITH NO. OF CRIMPS PER END			
		ACSR		ALUMINUM	COPPER	COLOR CODE	ACSR		ALUMINUM		COPPER	COLOR CODE	MD6	OH25	OUR840	Y750	Y35
		SIZE	STR.				SIZE	STR.									
	ES2W8W																
	ES2W6W	#4 (.250 DIA.) [6mm DIA.] #4 (.257 DIA.) [7mm DIA.]	6-1 7-1	#3 STR. (.260 DIA.) [7mm DIA.] #4 STR. (.232 DIA.) [6mm DIA.] #2 SOL. (.258 DIA.) [7mm DIA.]	#3 STR. (.260 DIA.) [7mm DIA.] #4 STR. (.232 DIA.) [6mm DIA.] #2 SOL. (.258 DIA.) [7mm DIA.]	ORANGE											
	ES2W4W																
C	ES2W2W																
	ES2R8W																
	ES2R6W	#2 (.316 DIA.) [8mm DIA.] #2 (.325 DIA.) [8mm DIA.]	6-1 7-1	#1 STR. (.328 DIA.) [8mm DIA.] #2 STR. (.292 DIA.) [7mm DIA.] #1 COMPT. (.299 DIA.) [8mm DIA.] #2 COMPT. (.271 DIA.) [7mm DIA.]	#1 STR. (.328 DIA.) [8mm DIA.] #2 STR. (.292 DIA.) [7mm DIA.] #2 STR. (.320 DIA.) [8mm DIA.]	RED											
B	ES2R4W																

NOTES:

1. BARREL IS PARTIALLY FILLED WITH PENETROX™ AND SEALED.

2. TWO CRIMPS MADE SIMULTANEOUSLY.

3. MULTIPLE CRIMP DIE SET.

4. MATERIAL: CONNECTOR - ALUMINUM

5. DIMENSIONS IN BRACKETS [ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

6. INSTALLATION INSTRUCTIONS:

1. STRIP CABLE INSULATION 7/8" (STRIP LENGTH INDICATED ON INSULINK™). FOR BEST RESULTS, REMOVE COTTON BRAID FOR AN ADDITIONAL 3/4" ON WEATHERPROOF AND SE TYPE CONDUCTORS

2. SCRATCH BRUSHING OF ALUMINUM CONDUCTORS, BEFORE MAKING INSTALLATIONS, IS RECOMMENDED.

3. INSERT CONDUCTOR THRU CENTER OF CAP AND THEN PUSH CONDUCTOR SO THAT STRIPPED END SEATS IN CONNECTOR AND INSULATION ENTERS CAP.

4. USING PROPER TOOL, CRIMP BETWEEN GUIDE LINES. MAKE INNERMOST CRIMP FIRST AND CRIMP TOWARD END. REPEAT FOR OTHER-SIDE.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

INSULINK™	
ITEM NO:	N/A
CAT. NO:	ES (TABLE)
DRAWN BY:	JMC 09/02/1958
CHECKER:	TUM 10/15/58
DSN APPVL:	--
MFG APPVL:	--
QA APPVL:	--
MKT APPVL:	--
PROD FAM:	--
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	Released



DRAWING NO	REV
SD040874	A
SHEET 2 OF 4	

REV: PEO200