



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
INSTALLATION PLATE	.063 C.R.S.	GALVANIZED
SCREW, TORX PN. HD.	STEEL	ZINC PLATE
WIRE BARRIER TUBE	STEEL 1/2 EMT	
WIRE BARRIER TUBE	STEEL 3/4 EMT	
FLOOR CUP	.064 C.R.S.	GALVANIZED
FIRE BARRIER	FIRE BARRIER MAT'L	
FIRE BARRIER- LOWER	FIRE BARRIER MAT'L	
WIRING TUBE- COMM.	STEEL EMT	
WIRING TUBE- POWER	STEEL EMT	
SUPPORT PLATE	.078 C.R.S.	GALVANIZED
COLLAR TUBE	STEEL	ZINC PLATE
COLLAR PLATE	.063 C.R.S.	GALVANIZED
SCREW, PN. HD.	STEEL	ZINC PLATE

SYMBOL	REVISIONS	APP	DATE
2	REVISED MAT'L OF FIRE BARRIER PER DCN 13699 RCM	DJP	1/30/07
1	REVISED PER DCN #1106		4/2/92

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
PT-27 FIRE RATED POKE-THROUGH WITH INSTALLATION PLATE

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ±1/64	DR. BY JMN	APP. BY ESW
DECIMALS ±.005	TR. BY	SCALE .5:1
ANGLES ±2°	CHK'D BY TCM	DATE 8/6/91

DIMENSION SHEET FOR CAT. NO. PT27A

REPAIRABLE NON-REPAIRABLE

B

M-6989

2