



SPECTRA™

- ▶ Advanced LED Performance
- ▶ Two Housing Scales and Matching Bollard
- ▶ Clean, Comfortable Appearance

NEW LED



CodeLinkSM



SP1 Spec Sheet



SP2 Spec Sheet



SPB Spec Sheet

ARCHITECTURAL AREA LIGHTING

Spectra LED – Large

Transitional Design

Adaptable appearance is perfect for contemporary installations

Full Family Offering

Two housing sizes and matching bollard offer consistent whole-site solutions

High Performance LEDs

Superior technology provides longer life, beyond traditional light sources

Comfortable Appearance

Glare-free illumination during nighttime operation

Solid Construction

Durable and long lasting design provides worry-free maintenance



SP1



SP1-SAP1

ORDERING INFORMATION


1. LUMINAIRE

SP1
Spectra LED – Large Scale Housing

3. LENS ELEMENT

VL3 Type 3 distribution
VL5 Type 5 distribution

2. HOOD



ANG – Angled Hood

FLR – Flare Hood

STR – Straight Hood

DBL – Double Hood

4. LED/DRIVER

55LED-BW 42 LED array. (53.8 total input watts).
Bright white (5000K). 120 thru 277 volt. Type 3.

55LED-BW 42 LED array. (55.4 total input watts).
Bright white (5000K). 120 thru 277 volt. Type 5.

5. HOOD FINISH (OPTIONAL)

STS Stainless steel
COP Natural copper

Hood underside is unfinished to develop a patina.

6. COLOR

All 13 standard and 4 premium AAL colors available. For custom colors, please submit a 4-digit RAL number.

7. OPTIONS

AD5 SP1 installs over a 4"/100mm O.D. pole. This adapter installs between the fixture and a 5"/127mm O.D. pole.

LDL Lightly diffused lens

8. MOUNTING

AWM1 Wall mounted arm for SP1

SAP1 Arm mount for SP1. Designed to slip over a 4"/100mm O.D. pole.

TAP1 Twin arm mount for SP1. Designed to slip over a 4"/100mm O.D. pole.

Ordering Information Example

1. LUMINAIRE SP1 2. HOOD STR 3. LENS VL3 4. LED/DRIVER 55LED-BW 5. HOOD FINISH STS 6. COLOR BLK 7. OPTIONS — 8. MOUNTING AWM1



Spectra LED – Small

Transitional Design

Adaptable appearance is perfect for contemporary installations

Full Family Offering

Two housing sizes and matching bollard offer consistent whole-site solutions

High Performance LEDs

Superior technology provides longer life, beyond traditional light sources

Comfortable Appearance

Glare-free illumination during nighttime operation

Solid Construction

Durable and long lasting design provides worry-free maintenance



SP2



SP2-SAP2

ORDERING INFORMATION

1. LUMINAIRE

SP2

Spectra LED – Small Scale Housing

2. HOOD



ANG – Angled Hood



FLR – Flare Hood



STR – Straight Hood



DBL – Double Hood

3. LENS ELEMENT

GLA

Frosted glass diffuser

4. LED/DRIVER

18LED-BW

18 LED array. (20.9 total input watts). Bright white (5100K). 120 thru 277 volt. Symmetric distribution.

18LED-WW

18 LED array. (20.9 total input watts). Warm white (3500K). 120 thru 277 volt. Symmetric distribution.

9LED-BW

9 LED array. (12.2 total input watts). Bright white (5100K). 120 thru 277 volt. Asymmetric distribution.

9LED-WW

9 LED array. (12.2 total input watts). Warm white (3500K). 120 thru 277 volt. Asymmetric distribution.

7. OPTIONS

AD4

SP2 installs over a 3"/75mm O.D. pole. This adapter installs between the fixture and a 4"/100mm O.D. pole.

LDL

Lightly diffused lens

5. HOOD FINISH

(OPTIONAL)

STS Stainless steel

COP Natural copper

Hood underside is painted white.

6. COLOR

All 13 standard and 4 premium AAL colors available. For custom colors, please submit a 4-digit RAL number.

8. MOUNTING

AWM2

Wall mounted arm for SP2

SAP2

Arm mount for SP2. Designed to slip over a 4"/100mm O.D. pole.

TAP2

Twin arm mount for SP2. Designed to slip over a 4"/100mm O.D. pole.

Ordering Information Example

1. LUMINAIRE
SP2

2. HOOD
ANG

3. LENS
GLA

4. LED/DRIVER
18LED-BW

5. HOOD FINISH
COP

6. COLOR
BLK

7. OPTIONS
—

8. MOUNTING
SAP2



Spectra LED – *Bollard*

Transitional Design

Adaptable appearance is perfect for contemporary installations

Full Family Offering

Two housing sizes and matching bollard offer consistent whole-site solutions

High Performance LEDs

Superior technology provides longer life beyond traditional light sources

Comfortable Appearance

Glare-free illumination during nighttime operation

Solid Construction

Durable and long lasting design provides worry-free maintenance



SPB



SPB

ORDERING INFORMATION

1. LUMINAIRE

SPB

Spectra Bollard LED

2. LENS ELEMENT

GLA

Frosted glass diffuser

3. LED/DRIVER

12LED-BW

12 LED array. (14.8 total input watts). Bright white (5100K). 120 thru 277 volt. Symmetric distribution.

12LED-WW

12 LED array. (14.8 total input watts). Warm white (3500K). 120 thru 277 volt. Symmetric distribution.

6LED-BW

6 LED array. (8.0 total input watts). Bright white (5100K). 120 thru 277 volt. Asymmetric distribution.

6LED-WW

6 LED array. (8.0 total input watts). Warm white (3500K). 120 thru 277 volt. Asymmetric distribution.

4. HOOD FINISH

(OPTIONAL)

STS Stainless steel

COP Natural copper

Hood underside is painted white.

5. COLOR

All 13 standard and 4 premium AAL colors available. For custom colors, please submit a 4-digit RAL number.

6. OPTIONS

COP Copper spun over cast hood

STS Stainless steel spun over cast hood

LDL Lightly diffused lens

Ordering
Information
Example

1. LUMINAIRE
SPB

2. LENS
GLA

3. LED/DRIVER
6LED-BW

4. HOOD FINISH
STS

5. COLOR
BLK

6. OPTIONS
COP

