


DRAWING NO.
CWSC34420-01

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	11/28/2007 1:26:00 PM	NEW FORM!	14544	RLB	PRL



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ARE ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- MATERIAL:
FERRULES - COPPER
BRAID - TIN-PLATED COPPER
- FINISH: TIN-PLATE THE FERRULES
- MARKINGS ETCHED ONTO SURFACE OF FERRULES:
CATALOG NUMBER, MANUFACTURER'S MARK
- MARKINGS STAMPED INTO FERRULES:
"TRUCK" & "AXLE" AS SHOWN ON DRAWING
- AMPACITY: (30°C TEMP. RISE OVER 40°C AMBIENT)
360 AMPS - INDOOR
430 AMPS - OUTDOOR
- WEIGHT: 1.26 LBS.
- ALL BRAID CONTACT SURFACES TO BE COVERED WITH PENETROX™ 'E' OXIDE INHIBITOR PRIOR TO BRAID ASSEMBLY. (BY BOMBARDIER)
- RECOMMENDED BOLT TORQUE VALUE FOR 3/8"-16 BOLT: 240 IN.-LBS.

BOMBARDIER • 871001255

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175 MANCHESTER, NH 03109, USA FOR PRODUCT INFO = http://www.fciconnect.com	
BRAID ASSEMBLY	
ITEM NO: 10007769	
CAT. NO: BF20D13X90TNCGI	
DRAWN BY: PW	04/17/02
CHECKER: RJG	04/18/02
DSN APPVL: --	--
MFG APPVL: --	--
QA APPVL: J. BRODEUR	04/07/02
MKT APPVL: --	--
SCALE: 0.625	
PROD FAM: --	DRAWING NO
PROJECT #: --	REV
DOCUMENT TYPE: --	CWSC34420-01
REL LEVEL: Released	SHEET 1 OF 1

REV: PED200