



Quality Raintight Fittings

Applications

Use RACO Raintight Steel EMT Compression Fittings in wet locations to bond and secure EMT conduit to a box or enclosure, or couple two ends of EMT conduit. They have been designed to comply with the new UL raintight test requirements and to comply with the requirements of the 2008 NEC 358.42 and 314.15.

Features

- All steel construction ensures mechanical protection for the raceway.
- Fittings are available in 1/2" to 4" trade sizes, one of the most complete lines in the industry.
- Zinc electroplate finish provides for a durable, corrosion-resistant installation.
- Blue tinted compression nuts and "Wet Locations" markings allow inspecting authorities to immediately determine that the installation is up to code.
- All connectors are supplied with a factory installed knockout seal. No need to buy a separate gasket.
- No need to disassemble the fitting prior to installation. RACO Raintight Steel EMT Compression Fitting can be installed directly on the conduit from the carton. No need to waste time loosening compression nuts.
- No need for special tools or torque wrench to install properly. Install these fittings like any other steel EMT compression fitting.
- Extended threaded fitting ensures a flush fit when connecting conduit to a thicker box, such as an Enphase combiner.



2902RT



2912RT



2903RTE



2924RT

Compression Connectors

Catalog No.		Trade Size	Unit Ctn. Qty.	Ship Ctn. Qty.
Insulated	Uninsulated			
2912RT	2902RT	1/2"	50	250
2913RT	2903RT	3/4"	25	125
2914RT	2904RT	1"	15	75
2915RT	2905RT	1-1/4"	-	20
2916RT	2906RT	1-1/2"	-	10
2918RT	2908RT	2"	-	10
2960RT	2940RT	2-1/2"	-	1
2962RT	2942RT	3"	-	1
2964RT	2944RT	3-1/2"	-	1
2966RT	2946RT	4"	-	1
Uninsulated, Extended Thread				
2903RTE		3/4"	25	125
2904RTE		1"	15	75

Compression Couplings

Catalog No.	Trade Size	Unit Ctn. Qty.	Ship Ctn. Qty.
2922RT	1/2"	50	250
2923RT	3/4"	25	125
2924RT	1"	15	75
2925RT	1-1/4"	-	20
2926RT	1-1/2"	-	10
2928RT	2"	-	10
2950RT	2-1/2"	-	1
2952RT	3"	-	1
2954RT	3-1/2"	-	1
2956RT	4"	-	1



A Hubbell brand

©2024 Raco, a division of Hubbell, Inc. All rights reserved.
Hubbell, the Hubbell logo, and Raco are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.
www.hubbell.com/raco | racocustomerservice@hubbell.com | +1 (800) 992-7030

EP-RACO-SF-EN-02180 | REV 08/2024