

BURNDY INSTALLATION TOOLING (# OF CRIMPS OR INDENTS PER END)



REV	DATE	DESCRIPTION	ECO	BY	CHK.
F	2017-11-07 11:13:00 EST	UPDATED TOOLING TABLE AND ADDED REFERENCE TO 900 KCMIL COMPACT ALUMINUM	47757	pp	MB

COLOR CODE	DIE INFORMATION		HYDRAULIC			
	DIE INDEX	TYPE	Y39 Y750 PAT750	Y46 PAT46	Y45	Y60BHU
--	27AB	--	--	--	--	--
		NEST	--	P44D(2)	--	--
		INDENTOR	--	P48PR-1	--	--
YELLOW	936	YELLOW DIE SET	U39ART-2 (4)	U39ART-2 (4)	U39ART-2 (4)	L39ART-2 (2)
		NEST	--	--	--	--
		INDENTOR	--	--	--	--

CATALOG NUMBER	CONDUCTOR RANGE		WIRE STRIP LENGTH	DIE INDEX
	BARREL 'A'	BARREL 'B'		
YRB36U25	600 kcmil	1/0 AWG	2-5/16"	27AB
YRB36U28		4/0 AWG		
YRB36U29		250 kcmil		
YRB36U30		300 kcmil		
YRB36U31		350 kcmil		
YRB36U32		400 kcmil		
YRB36U34		500 kcmil		
YRB36U34		936		

CATALOG NUMBER	CONDUCTOR RANGE		WIRE STRIP LENGTH	DIE INDEX
	BARREL 'A'	BARREL 'B'		
YRB39U26	700 kcmil 750 kcmil 900 kcmil CMPT AL	2/0 AWG	2-5/16"	27AB
YRB39U28		4/0 AWG		
YRB39U29		250 kcmil		
YRB39U30		300 kcmil		
YRB39U31		350 kcmil		
YRB39U32		400 kcmil		
YRB39U34		500 kcmil		
YRB39U36		600 kcmil		

CATALOG NUMBER	CONDUCTOR RANGE		WIRE STRIP LENGTH	DIE INDEX
	BARREL 'A'	BARREL 'B'		
YRB44U28	1000 kcmil	4/0 AWG	2-5/16"	27AB
YRB44U29		250 kcmil		
YRB44U30		300 kcmil		
YRB44U31		350 kcmil		
YRB44U32		400 kcmil		
YRB44U34		500 kcmil		
YRB44U36		600 kcmil		
YRB44U39		700-750 kcmil 900 kcmil CMPT AL		



TYPICAL LETTERING VIEW

NOTES:

1. MATERIAL: ALUMINUM
2. FINISH: TIN PLATED
3. BARRELS ARE PARTIALLY FILLED WITH PENETROX AND SEALED.
4. SCRATCH BRUSHING OF ALL CONDUCTORS BEFORE MAKING INSTALLATION IS RECOMMENDED
5. NOT FOR USE WITH COPPER TO COPPER APPLICATIONS.
6. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
7. CATALOG #PT6515 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y45 SERIES TOOLS.
8. CATALOG #PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.
9. INDEX NUMBER 936 GIVES A HEXAGONAL CRIMP.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)  CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)  FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>	HYREDUCER <sup>RM</sup>		
	ITEM NO:	N/A	
	CAT. NO:	YRB-U- (TABLE)	
	DRAWN BY:	R.PERREAULT 04/30/96	
	CHECKER:	J.MICHAUD 05/01/96	
	DSN APPVL:	C.PALAGI 11/13/95	
	MFG APPVL:	N/A --	
	QA APPVL:	D.VARIO 12/21/95	
	MKT APPVL:	L.HERRON 11/28/02	
	PROD FAM:	--	
PROJECT #:	--	SIZE	DRAWING NO SD074136 SCALE: 1:1 SHEET 5 OF 5
DOCUMENT TYPE:	Sales	D	
REL LEVEL:	Released	F	