


RACO' TAYMAC' BELL

CONDUIT HANGERS

Conduit Hangers with Nut and Bolt, Steel N/A

B84





Catalog #: 2057

APPLICATIONS

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls N/A

PRODUCT FEATURES

Furnished with a nut and bolt to speed installation Pregalvanized finish provides corrosion protection

UL LISTED

Standard 514B (trade size 0-9)

CULUS

Canada (trade size 0-9)

GENERAL PRODUCT INFORMATION

 Trade Size:
 6

 Rigid/IMC Size:
 2-1/2 in.

 EMT Size:
 2-1/2 in.

 Max Load Lbs.:
 125

DRAWING DIMENSIONS

 Dimension A:
 2.87 in.

 Dimension B:
 1.25 in.

 Dimension C:
 .63 in.

 Dimension D:
 .31 in.

PACKAGING

 CKAGING

 Package Type:
 Carton

 Ship Carton Qty.:
 25

 Product UPC-A Labeled:
 No

 Weight (Lbs. Per/C):
 31.50

 Ship Carton Length (in.):
 10.00

 Ship Carton Width (in.):
 7.25

 Ship Carton Height (in.):
 8.00

 Ctn Weight (Lbs.):
 7.88

UPC Number: 050169020579
I2of5: 50050169020574