



Commercial Construction
and Industrial Automation

480V SINGLE PHASE 3KVA PANEL-TRAN ZONE POWER CENTER

NEW!

Our latest Zone power center model combines an Acme encapsulated distribution transformer with a power panel assembly in a single NEMA 3R enclosure. Pre-wired and pre-tested, this power center provides versatility, indoor/outdoor convenience and ease-of-use with cost-effectiveness. Just add breakers. Suitable for use as service entrance equipment



Acme Electric Panel-Tran Features

Primary Voltage


- 480 Volts; single phase, 60 Hz
- 2 - 5% BNFC taps

Secondary Voltage

- 240/120 Volts single phase
- 60Hz three wire system

Insulation Class:

- 180 C, UL Listed system
- 115 C rise
- Accommodates one-inch, 1 or 2 pole common trip breakers
- Duplex secondary branch circuit breakers
- Ground fault circuit breakers
- NEMA 3R enclosure
- 10 Year limited warranty
- Also available: 5, 7.5, 10, 15, 25kVA



Encapsulated construction

Primary circuit breakers provided

Secondary main circuit breakers provided

Snap-in or bolt-in circuit breakers

UL Listed system

NEMA 3R Rated



kVA	CATALOG #	MAXIMUM SECONDARY CIRCUITS		HEIGHT	WIDTH	DEPTH	Lbs. (Kg.)
		120V 1-POLE	240V 2-POLE				
Panel-Tran Zone Power Center							
3	PT061150003LS	8	4	32.13 (8.16)	15.88 (40.3)	11.00 (27.9)	120 (54.4)



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

ACME ELECTRIC
N85 W12545 Westbrook Crossing
Menomonee Falls, WI 53051
www.hubbell.com/acmeelectric/en

