




CONDUIT HANGERS

Conduit Hangers with Nut and Bolt, Steel
N/A

B84



Catalog #: 2058

APPLICATIONS

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls
N/A

PRODUCT FEATURES

Furnished with a nut and bolt to speed installation
Pregalvanized finish provides corrosion protection

UL LISTED

Standard 514B (trade size 0-9)

CULUS

Canada (trade size 0-9)

GENERAL PRODUCT INFORMATION

| | |
|-----------------|-------|
| Trade Size: | 5 |
| Rigid/IMC Size: | 2 in. |
| EMT Size: | 2 in. |
| Max Load Lbs.: | 100 |

DRAWING DIMENSIONS

| | |
|--------------|----------|
| Dimension A: | 2.25 in. |
| Dimension B: | 1.00 in. |
| Dimension C: | .04 in. |
| Dimension D: | .31 in. |

PACKAGING

| | |
|---------------------------|----------------|
| Package Type: | Carton |
| Ship Carton Qty.: | 50 |
| Product UPC-A Labeled: | No |
| Weight (Lbs. Per/C): | 25.20 |
| Ship Carton Length (in.): | 10.60 |
| Ship Carton Width (in.): | 12.50 |
| Ship Carton Height (in.): | 8.50 |
| Ctn Weight (Lbs.): | 12.60 |
| UPC Number: | 050169020586 |
| I2of5: | 50050169020581 |