




**CONDUIT HANGERS**

Conduit Hangers with Nut and Bolt, Steel  
N/A

B84



Catalog #: 2059

**APPLICATIONS**

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls  
N/A

**PRODUCT FEATURES**

Furnished with a nut and bolt to speed installation  
Pregalvanized finish provides corrosion protection

**UL LISTED**

Standard 514B (trade size 0-9)

**CULUS**

Canada (trade size 0-9)

**GENERAL PRODUCT INFORMATION**

Trade Size:	7
Rigid/IMC Size:	3 in.
EMT Size:	3 in.
Max Load Lbs.:	165

**DRAWING DIMENSIONS**

Dimension A:	3.50 in.
Dimension B:	1.25 in.
Dimension C:	.63 in.
Dimension D:	.31 in.

**PACKAGING**

Package Type:	Carton
Ship Carton Qty.:	25
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	36.30
Ship Carton Length (in.):	10.60
Ship Carton Width (in.):	12.50
Ship Carton Height (in.):	8.50
Ctn Weight (Lbs.):	9.08
UPC Number:	050169020593
I2of5:	50050169020598