



# Compression Splice Conventional (Hex Die) Full Tension

by FARGO  
Catalog ID: 20850

Compression Splice, Conventional, Full Tension, for AAC, Dia. Range  
0.773-0.819

\* Representative image

## Product Details

### General

Aluminum Die	24AH
Compression Method	Conventional
Inhibitor Loaded	No
Material	Aluminum Alloy
Press Minimum	60 to
Tension Range	0 lb
UPC	096359250104

### Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	15.7 in
Weight	0.980 lb

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Conductor Compatibility	AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter - Maximum	0.819 in
Conductor Diameter - Minimum	0.773 in
Conductor Diameter Range	0.773 - 0.819
Conductor Type	AAC
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

### Certifications and Compliance

UL Listed	No
-----------	----

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)