



\* Representative image

# PDV-100 Arrester (15.3 kV Uc, CVBC Hardware)

by OHIO BRASS  
Catalog ID: 214215CVBC

IEC Class 1 Polymer Housed Surge Arrester

- Over 30 years of excellent field performance with over 36 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

## Product Details

### General

Application	Distribution
Bracket Type	None
Cantilever Bending Strength - Max.	2.04 in lbs (18.05 N-M)
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Class 1
UPC	096359434313

### Dimensions

Height	8.5 in
Stud Type	M12

### Electrical Ratings

Creep and Leakage Distance	780 mm
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	58.5 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 45.1 kV @ 1.5 kA</li> <li>• 47 kV @ 3 kA</li> <li>• 48.9 kV @ 5 kA</li> <li>• 52.7 kV @ 10 kA</li> <li>• 58.2 kV @ 20 kA</li> <li>• 67.5 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	38.8 kV
Minimum Strike	270.0 mm
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000

## Certifications and Compliance

Industry Standard(s)	IEC
----------------------	-----

**For further technical assistance, please contact us**

### **Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

### **International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)