

LNC2

LITEPAK

MICRO STRIKE

LITEPAK MICRO STRIKE



The LitePak LNC2 LED is designed for perimeter illumination for safety, security and identity. The LNC2 achieves up to 85% energy savings over traditional lighting sources and includes Micro Strike optics for superior distribution patterns with high lumens per watt.

- Bluetooth occupancy sensor and NX wireless control options available for greater control and energy savings.
- Battery backup option for egress applications provides 1 fc average over path of egress at typical mounting heights
- Standard (down to 0°C) and cold pack (down to -30°C) battery backup options available
- Energy-efficient LED systems ranging from 10-45 watts with up to 85% energy savings over traditional sources
- Available in 3000K, 4000K and 5000K LEDs as well as Amber
- Full cut-off, neighbor friendly, optics with no uplight (U0)
- Type III and IV distributions available for a variety of application needs
- Versatile mounting options recessed box or surface conduit wiring
- Quick-mount adapter allows easy installation/maintenance
- 347V and 480V versions for industrial applications and Canada
- Optional photocontrol for additional energy savings
- Five year warranty

LNC2 LITEPAK MICRO STRIKE



HUBBELL®
Outdoor Lighting

© 2022 Hubbell Outdoor Lighting, a division of Hubbell Lighting, Inc. Specifications subject to change without notice.
701 Millennium Blvd • Greenville, SC 29607 / Tel 864.678.1000 / Website www.hubbelloutdoor.com


ORDERING INFORMATION

SERIES	LIGHT ENGINE	CCT/CRI	DISTRIBUTION	VOLTAGE	MOUNTING
LNC2 Small LitePak LNC2	48L-10 1000 lumens 48L-15 2000 lumens 48L-20 2500 lumens 48L-25 3500 lumens 48L-35 4500 lumens 48L-45 5500 lumens P15 15w Prismatic P25 25w Prismatic P35 35w Prismatic	3K7 3000K, 70 CRI 4K7 4000K, 70 CRI 5K7 5000K, 70 CRI AM Amber	3 Type 3 4W Type 4 Wide	UNV 120-277V 120 120V 208 208V 240 240V 277 277V 347 347V ⁷ 480 480V ⁷	Leave blank for down NV Inverted ³


FINISH	CONTROL OPTIONS	ADDITIONAL OPTIONS	NOTES
BLT Black Matte Textured BLS Black Gloss Smooth DBT Dark Bronze Matte Textured DBS Dark Brone Gloss Smooth GTT Graphite Matte Textured LGS Light Grey Gloss Smooth PSS Platinum Silver Smooth WHT White Matte Textured WHS White Gloss Smooth VGT Verde Green Textured <u>Color Option</u> CC Custom Color	PC Photocontrol ⁴ BTSO12F *Bluetooth Programmable, PIR Occupancy/Daylight Sensor, up to 12' mounting height ⁵ NXWE NX hubbNET Wireless Radio Module NXRM2, without Sensor NXSPW12F NX hubbNET Wireless Enabled Integral NXSPM2-OMNI PIR Occupancy Sensor, 12' mounting height 2DR Dual Driver (18L - 700mA only) ^{1,2} 2PF Dual Power Feed (18L -700mA only) ^{1,2}	F Fusing (specify voltage) EH Battery Backup Unit with Heater (-30°C) ⁶ E Battery Backup Unit (0°C) ⁶ CS Comfort Shield (N/A with Prismatic Refractor) 2DR Dual Driver ^{1,2} 2PF Dual Power Feed ^{1,2} CH Surface Conduit Hubs	<i>Items with a grey background can be done as a custom order. Contact brand representative for more information</i> NOTES 1 Available in 35 & 45W 2 Options cannot be combined with controls or PC option 3 Not available with occupancy sensor, battery backup or prismatic refractor options 4 PC comes in standard housing 5 BTS, NX and CH options come in medium back box 6 E and EH come in large back box 7 347V & 480V only available in 25 and 35W

DIMENSIONS

- A: 5.54"/141 mm
- B: 10.164"/258 mm
- C: 6.33"/161 mm
- D: 7.64"/196 mm
- E: 9.10"/231 mm



PHOTOMETRY



45W configuration at 20ft mounting height