

Clear and Black Cold Shrink

Rated for 2000 Volts

Burndy proudly introduces enhancements to our existing low voltage silicone rubber sleeves.

Cold applied shrink products are made of specially formulated silicone rubber and offer excellent insulation and moisture resistant sealing for in-line cable connector systems. The rubber sleeves are factory expanded over a removeable, plastic ripcord housing. Installs quickly and easily. Operating temperature range: -40°C to 105°C.



Features

- Length of tube is consistent before and after application
- Easy, safe installation
- Suitable for wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture resistant seal
- Indoor and outdoor applications
- Rip and Grip! Does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- cUL insulating cover for wire connectors tested in accordance to UL 486A/B
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable



CLEAR AND BLACK COLD SHRINK



Clear Cold Shrink

Inspectability to verify correct tool/die combination

Catalog Number	Length	Jacket OD Range	Aluminum Code	Copper Code	Copper Flex including Telco Flex
CCSC110600	6"	.39" - .80"	#1 - 3/0 AWG	#1 AWG - 250 kcmil	#2 - 4/0 Flex
CCSC110800	8"	.39" - .80"	—	#1 AWG - 250 kcmil	#2 - 4/0 Flex
CCSC146600	6"	.70" - 1.05"	—	250 kcmil - 500 kcmil	4/0 Flex - 350 Flex
CCSC146900	9"	.70" - 1.05"	—	250 kcmil - 500 kcmil	4/0 Flex - 350 Flex
CCSC200600	6"	.90" - 1.28"	—	400 kcmil - 750 kcmil	350 Flex - 500 Flex
CCSC200900	9"	.90" - 1.28"	—	400 kcmil - 750 kcmil	350 Flex - 500 Flex
CCSC256600	6"	1.22" - 2.01"	1000 - 1250 kcmil	1000 kcmil - 1500 kcmil	750 Flex (777)
CCSC256900	9"	1.22" - 2.01"	1000 - 1250 kcmil	1000 kcmil - 1500 kcmil	750 Flex (777)

**TELCOFLEX® L2 Telecom Power Wire and Cable is a registered brand of Southwire
UL Listed for Direct Burial



Black Cold Shrink

Catalog Number	Length	Jacket OD Range	Aluminum Code	Copper Code	Copper Flex including Telco Flex
BCSC110600	6"	.39" - .80"	#1 - 3/0 AWG	#1 AWG - 250 kcmil	#2 - 4/0 Flex
BCSC110800	8"	.39" - .80"	—	#1 AWG - 250 kcmil	#2 - 4/0 Flex
BCSC146600	6"	.70" - 1.05"	—	250 kcmil - 500 kcmil	4/0 Flex - 350 Flex
BCSC146900	9"	.70" - 1.05"	—	250 kcmil - 500 kcmil	4/0 Flex - 350 Flex
BCSC200600	6"	.90" - 1.28"	—	400 kcmil - 750 kcmil	350 Flex - 500 Flex
BCSC200900	9"	.90" - 1.28"	—	400 kcmil - 750 kcmil	350 Flex - 500 Flex
BCSC256600	6"	1.22" - 2.01"	1000 - 1250 kcmil	1000 kcmil - 1500 kcmil	750 Flex (777)
BCSC256900	9"	1.22" - 2.01"	1000 - 1250 kcmil	1000 kcmil - 1500 kcmil	750 Flex (777)

**TELCOFLEX® L2 Telecom Power Wire and Cable is a registered brand of Southwire
UL Listed for Direct Burial



A proud member of the Hubbell family.

©2023 Burndy. All rights reserved.
Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated.
All other trademarks are the property of their respective owners.
www.hubbell.com/burndy | Customer Service 1-800-346-4175
International 603-647-5299 | Canada 1-800-465-7051

LI-BURC-SF-EN-00987 | REV 07/2023