



* Representative image

Under-Oil Arrester (2.55 kV MCOV, 3001 Hardware)

by OHIO BRASS
Catalog ID: 2211033001

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge Arrester

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

Product Details

General

Application	Under Oil
Mounting Hardware	Bracket
Mounting Type	Bracket
UPC	096359416951

Dimensions

Length	3.71 in
--------	---------

Electrical Ratings

BIL	75 kV
Duty Cycle	3 kV
Frequency Rating	48-62 Hz
MCOV	2.55 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	10.43
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 8.43 kV @ 1.5 kA • 8.88 kV @ 3 kA • 9.29 kV @ 5 kA • 9.97 kV @ 10 kA • 11.04 kV @ 20 kA
Maximum Switching Surge Protective Level @ 500A	7.87

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com