



* Representative image

Under-Oil Arrester (5.1 kV MCOV, 3001 Hardware)

by OHIO BRASS
Catalog ID: 2211053001

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge Arrester

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

Product Details

General

Application	Under Oil
Mounting Hardware	Bracket
Mounting Type	Bracket
UPC	096359416975

Dimensions

Length	5.73 in
--------	---------

Electrical Ratings

BIL	75 kV
Current Rating	2000 A
Duty Cycle	6 kV
Frequency Rating	48-62 Hz
MCOV	5.1 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	20.9
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 16.83 kV @ 1.5 kA • 17.72 kV @ 3 kA • 18.54 kV @ 5 kA • 19.89 kV @ 10 kA • 22.02 kV @ 20 kA
Maximum Switching Surge Protective Level @ 500A	15.69

Logistics

Pallet Quantity	160 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com