



\* Representative image

## Under-Oil Arrester (8.4 kV MCOV, 3002 Hardware)

by OHIO BRASS  
Catalog ID: 2211093002

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge Arrester

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

### Product Details

#### General

Application	Under Oil
Mounting Hardware	No Bracket
Mounting Type	No Bracket
UPC	096359417026

#### Dimensions

Length	6.01 in
--------	---------

#### Electrical Ratings

BIL	95 kV
Current Rating	1000 A
Duty Cycle	10 kV
Frequency Rating	48-62 Hz
MCOV	8.4 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	30.33
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 29.03 kV @ 1.5 kA</li> <li>• 30.57 kV @ 3 kA</li> <li>• 31.98 kV @ 5 kA</li> <li>• 34.31 kV @ 10 kA</li> <li>• 37.98 kV @ 20 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	27.07

#### Logistics

Pallet Quantity	160 EA
-----------------	--------

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)