

TAIL END UNIT Type TEU2

- Monitors the pre-start alarm tones on the V-line from the controller
- Acknowledges a pre-start alarm via an S-line and Dupline/SILBUS
- Continuously monitors the pre-start alarm hardware and cabling



#### **DESCRIPTION**

The Tail End Unit type TEU2 is situated at the boot end of the conveyor. Its sole purpose is to monitor the pre-start alarm tones on the V line from the controller at the drive head.

If a valid pre-start alarm tone is received from the controller, the TEU2 will divide this tone frequency by eight and return the new, lower tone back to the controller via the S line. This process of modifying the pre-start tone and returning it to the controller allows the controller to verify that the pre-start alarm tone did not reach the boot end of the conveyor.

The TEU2 can also provide a pre-start alarm detected (confirmed) output that can be used to drive a Dupline field bus standard single channel digital transmitter or a safety transmitter. This feature can be used to monitor the pre-start alarm signal via an alternate return path.

If a pre-start alarm system end-of-line under-voltage is detected, then that output can also be used by the TEU2 to drive a Dupline field bus standard single channel digital transmitter or a safety transmitter. This feature can be used to continuously monitor the integrity of the pre-start alarm hardware and cabling, instead of just during a pre-start alarm.

### **TYPICAL APPLICATIONS**

The Tail End Unit TEU2 can only be used in a PSACS1 system for monitoring pre-start alarm tones and end-of-line voltage.

### **CERTIFICATION**


The Tail End Unit type TEU2 is IECEx certified for use in hazardous areas in accordance with the certificate IECEx TSA 07.0021X.

# **INTRINSICALLY SAFE INFORMATION**

SILBUS	li = 3 A	Ui = 12.6V		
	Ci = 0uF	Li = 0uH		
PSACS1 X1	li = 3 A	Ui = 12.6V		
	Ci = 0uF	Li = 0uH		
PSACS1 X2, X3, X4, X5	li = 3 A	Ui = 12.6V		
	Ci = 0uF	Li = 0uH		
PSACS1 TB1	Ii = 3 A	Ui = 12.6V		
	Ci = 0uF	Li = 0uH		



### **CONNECTION & MOUNTING DIAGRAMS**




LED1 (Green) and LED2 (Yellow) are on the other side of the PCB (not shown here).

If LED1 (Green) is flashing once every 3 seconds, this indicates that the PCB is working normally.

LED1 turns on solidly when the unit detects a PSA request signal.

LED2 (Yellow) will turn on while the PBC detects a low line voltage (< 7.5V).



### **SPECIFICATIONS**

GENERAL SPECIFICATIONS				
Gland size	To fit cable 16mm <sup>2</sup>			
Size	180 (W) x 160 (H) x 115mm (D)			
	7 (W) x 6.3 (H) x 4.5inches (D)			
Ingress Protection	IP55			
Enclosure material	Stainless steel			
Operating Temperature	0°C - 40°C (32°F - 104°F)			
Storage Temperature	0°C - 40°C (32°F - 104°F)			
Enclosure Type	ENCL08			

### **PIN ASSIGNMENT**

X1 CONNECTION DETAILS				
4 Pin	Colour	Description		
1	BLUE	POWER +		
2	RED	SIGNAL		
3	BLACK	POWER -		
4	YELLOW	VOICE		
X2, X3 CONNECTION DETAILS				
6 Pin	Colour	Description		
6	BROWN	DUPLINE SIGNAL		
5	BLACK	SCLK		
2	YELLOW	CONTACT INPUT		
3	BLUE	DUPLINE COMMON		
1	PINK	NOT CONNECTED		
4	WHITE	VREG		
X4, X5 CONNECTION DETAILS				
6 Pin	Colour	Description		
6	BROWN	DUPLINE SIGNAL		
5	GREEN	CONFIGURATION RX		
2	YELLOW	CONFIGURATION TX		
3	GREY	DUPLINE COMMON		
1	PINK	CONTACT INPUT SOURCE		
4	WHITE	CONTACT INPUT DRAIN		

# **ORDERING DETAILS**

DESCRIPTION	ORDER CODE
TAIL END UNIT C/W LED	TEU301
DISPLAY	



**AUSTDAC PTY LTD.** Head office: Castle Hill, Australia Mackay, QLD, Australia

Pittsburgh, USA **Burton Upon Trent, UK**  +61 (0) 2 8851 5000

+61 (0) 7 4955 2777 +1 888 254 9155 (Toll free in US & Canada) +44 (0) 2 1283 500 500