




CONDUIT HANGERS

Conduit Hangers with Nut and Bolt, Steel
N/A

B84



Catalog #: 2060

APPLICATIONS

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls
N/A

PRODUCT FEATURES

Furnished with a nut and bolt to speed installation
Pregalvanized finish provides corrosion protection

UL LISTED

Standard 514B (trade size 0-9)

CULUS

Canada (trade size 0-9)

GENERAL PRODUCT INFORMATION

Trade Size:	8
Rigid/IMC Size:	3-1/2 in.
EMT Size:	3-1/2 in.
Max Load Lbs.:	200

DRAWING DIMENSIONS

Dimension A:	4.00 in.
Dimension B:	1.25 in.
Dimension C:	.63 in.
Dimension D:	.31 in.

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	10
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	38.80
Ship Carton Length (in.):	10.00
Ship Carton Width (in.):	7.25
Ship Carton Height (in.):	8.00
Ctn Weight (Lbs.):	3.88
UPC Number:	050169020609
I2of5:	50050169020604