



Compression Splice Conventional (Hex Die) Full Tension

by FARGO
Catalog ID: 20609

Compression Splice, Conventional, Full Tension, for AAC, Dia. Range
0.551-0.593



* Representative image

Product Details

General

Aluminum Die	75AH
Compression Method	Conventional
Inhibitor Loaded	No
Material	Aluminum Alloy
Press Minimum	12 to
Tension Range	0 lb
UPC	096359459590

Dimensions

Adjustment Step	0 in
Assembly Rating (Ultimate)	0 lb
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	11.1 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	AAC-Valerian-250-19;AAC-Laurel-266.8-19
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter - Maximum	0.593 in
Conductor Diameter - Minimum	0.551 in
Conductor Diameter Range	0.551 - 0.593
Conductor Type	AAC
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Certifications and Compliance

UL Listed	No
-----------	----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com