



\* Representative image

# Suspension Clamp

by ANDERSON  
Catalog ID: 2706513001

The 270 series suspension clamp is a trunnion type suspension clamp designed for use on ground wire applications with galvanized steel. The 270 series clamp is designed for use on tangent suspension spans with horizontal or vertical post insulators. Keeper is reversible for proper fit on different size ground wires. SUSPENSION, TRUNNION D.I., .5-1.06

- Anti-static spring can be supplied by adding "ARIV" to catalog number. Example, 2706513001ARIV

## Product Details

### General

|  |                               |
|--|-------------------------------|
| Bolt Installation Torque (Recommended) | 480 in-lbs                    |
| Material - Clamp                       | Ductile Iron                  |
| Material - Hardware                    | Galvanized Steel              |
| Product Category                       | Trunnion Clamp                |
| Strength Rating - Ultimate Body        | 2800 lb                       |
| Type                                   | Ground Wire Suspension Clamps |
| UPC                                    | 096359261797                  |
| With Anti-Static Springs               | No                            |

### Dimensions

|                                       |             |
|---------------------------------------|-------------|
| Angle - Take-Off Maximum              | 15 °        |
| Bolt Diameter                         | 0.500 in    |
| Clamping - Maximum                    | 1.06 in     |
| Clamping - Minimum                    | 0.5 in      |
| Diameter - Insulator Attachment Holes | 0.609375 in |
| Length                                | 5.25 in     |
| Weight                                | 2.75 lb     |
| Width                                 | 3.875 in    |

### Electrical Ratings

|                     |             |
|---------------------|-------------|
| Voltage Application | Ground Wire |
|---------------------|-------------|

### Conductor Related

|                |           |
|----------------|-----------|
| Clamping Range | 0.5- 1.06 |
|----------------|-----------|

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com