



**Commercial, Industrial
and Residential Electrical Products**

4-11/16 In. Square Box, 2-1/8 In. Deep, (1) STAB-iT® II Connector, "M" Bracket for Stud Mounting, with Grounding Pigtail and Cable Management Clip

Catalog #:
252MSCM



FEATURE BENEFIT

The fastest way to install MC. Unique built-in connector saves time and reduces worksite waste. Get MC-PCS ready, right out of the carton.

PRODUCT FEATURES

- Designed for quick installation of flex, MC, MCI, MCI-A, MC-PCS, AC, and HCF Cable
- Accepts cable sizes from 14/2 up to 10/3 for most cable types
- **3 TIMES FASTER than traditional connectors**
- 4-11/16 In. sq. boxes are 2-1/8 In. deep and includes 1 STAB-IT II connector
- Each STAB-IT II connector accommodates three cables
- Includes built-in cable management clip, offering first means of support
- **UL listed for use without a plastic bushing (except for AC Cable)**
- Pre-installed 8 In. solid #12 pigtail for faster installation
- Includes "M" style bracket for stud mounting
- Suitable for use without a bonding jumper in circuits up to 600 volts
- Improved design allows each cable to easily be removed, allows connector to be reused
- Designed in USA

APPLICATIONS

- For any job using flexible armored cable
- Ideal for Pre-Fab

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number: 50169995495
 Ea Length/Depth (in.): 2.693
 Ea Width (in.): 6.546
 Ea Height (in.): 4.88
 Wt. Ea. (Lbs.): 1.453
 Package Type: Loose
 Product UPC-A Labeled: No

PACKAGING

Case 12of5: 50050169995490
 Standard Carton Qty: 25
 Min Order Qty: 25

CABLE TYPES AND RANGES FOR STAB-IT® II CLAMP

CABLE TYPE	CABLE RANGE	CABLE DIAMETER RANGE
AC STEEL	14-2, 14-3 14-4, 12-2, 12-3, 12-4, 10-2, 10-3	0.44" - 0.62"
HCF AC STEEL	12-2, 12-3, 10-2, 10-3	
AC ALUMINUM	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3	0.42" - 0.62"
HCF AC ALUMINUM	12-2, 12-3, 12-4, 10-2, 10-3	
MC STEEL	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3	
MCI-A STEEL	14-2, 12-2, 12-3, 12-4, 10-2, 10-3	
HCF MCI-A STEEL	12-2, 12-3, 10-2	0.38" - 0.62"
MC-PCS STEEL	12-2/16-2, 12-3/16-2, 10-2/16-2	
MC ALUMINUM	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3	
MCI-A ALUMINUM	14-2, 14-3, 14-4, 12-2, 12-3, 12-4, 10-2, 10-3	
HCF MCI-A ALUMINUM	12-2, 12-3, 12-4, 10-2, 10-3	0.38" - 0.62"
MC-PCS ALUMINUM	12-2/16-2, 12-3/16-2, 10-2/16-2	
3/8 TRADE SIZE FLEX. RWFMC CONDUIT STEEL & ALUMINUM Anti Short Bushing Required		

Cable Armor must comply with NEC 250.96

To install larger diameter cables (if needed) loosen up screw, insert cable, tighten up screw and push in cable until it snaps into place as shown on instructions.

To remove cable: Loosen up screw, pull spring clip away from cable and pull cable out. See instruction sheet.

To install more cables use any of the knockouts with RACO® REDI-LOC® connector.



Revision 1, June 2019



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

