

2661 - Acceptable Uses

AC Cable No. 10-2 Steel	Maximum Diameter 0.598 in.
AC Cable No. 14-2 Steel	Minimum Diameter 0.460 in.
AC Cable No. 10-2 Aluminum	Maximum Diameter 0.565 in.
AC Cable No. 14-2 Aluminum	Minimum Diameter 0.480 in.
MCI Cable No. 10-3 Steel	Maximum Diameter 0.600 in.
MCI Cable No. 14-2 Steel	Minimum Diameter 0.469 in.
MCI Cable No. 10-3 Aluminum	Maximum Diameter 0.610 in.
MCI Cable No. 14-2 Aluminum	Minimum Diameter 0.470 in.
MC-PCS Cable No. 10-3 Steel	Maximum Diameter 0.600 in.
MC-PCS Cable No. 14-2 Steel	Minimum Diameter 0.469 in.
MC-PCS Cable No. 10-3 Aluminum	Maximum Diameter 0.610 in.
MC-PCS Cable No. 14-2 Aluminum	Minimum Diameter 0.470 in.
MCI-A Cable No. 10-3 Aluminum	Maximum Diameter 0.610 in.
MCI-A Cable No. 14-2 Aluminum	Minimum Diameter 0.370 in.
*HCF MCI-A Cable 10-2 Aluminum	Maximum Diameter 0.495 in.
*HCF MCI-A Cable 12-2 Aluminum	Minimum Diameter 0.418 in.
3/8 (12) Steel or Aluminum FMC	