


**STRAIN RELIEF CONDUIT AND CORD CONNECTORS - ALUMINUM**Straight Strain Relief Cord Connectors Aluminum
N/A**B60**

Catalog #: 4801-0

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
 Aluminum liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

Aluminum construction provides a corrosion resistant installation
 Patented Gotcha® ring incorporates a split hinge design to prevent friction and to provide strain relief
 Neoprene grommet
 Knurled compression nut allows the fittings to be hand tightened to UL requirements
 Gotcha® ring is color-coded for sizing identification
 N/A

UL LISTED

Standard 514B

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 1/2 in.
 Cable Range: .062 - .125
 Color Code: Green
 Form Size: 2

DRAWING DIMENSIONS

Dimension A: 1.13 in.
 Dimension B: .55 in.
 Dimension C: 1.10 in.
 Dimension D: .64 in.
 Dimension E: A/C 1.11 in., A/F 1.00 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 25
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 5.90
 Ship Carton Length (in.): 6.25
 Ship Carton Width (in.): 4.50
 Ship Carton Height (in.): 4.25
 Ctn Weight (Lbs.): 1.48
 UPC Number: 050169480106
 I2of5: 50050169480101