


**90 DEGREE GROUNDING CONDUIT AND CORD CONNECTORS****90° Insulated Connector with Ground Lug, Steel/Malleable Iron**  
N/A**B52**

Catalog #: 3541-3

**APPLICATIONS**

For use in outdoor or indoor locations on flexible metallic liquidtight conduit, when installation of a copper or aluminum external bonding jumper is required  
RACO grounding liquidtight connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

**PRODUCT FEATURES**

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts  
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service  
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening  
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground  
All metallic components are zinc electro plated for added corrosion protection  
Malleable Iron castings mate with other components perfectly without strain or distortion  
3/8 in. to 4 in. Malleable iron bodies  
3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts

**UL LISTED**

Standard 514B, UL Listed E195969

**cULus LISTED****GENERAL PRODUCT INFORMATION**

Trade Size: 3/8 in.  
Min. Grounding Wire Capacity: #14 SOL.  
Max Grounding Wire Capacity: #4 STR.

**DRAWING DIMENSIONS**

Dimension A: 1-3/64 in.  
Dimension B: 35/64 in.  
Thread Spec. B: 1/2 in. - 14 NPT  
Dimension C: 1-3/8 in.  
Dimension D: 1-7/16 in.  
Dimension E: 25/32 in.

**PACKAGING**

Package Type: Carton  
Ship Carton Qty.: 25  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 28.50  
Ship Carton Length (in.): 10.00  
Ship Carton Width (in.): 5.25  
Ship Carton Height (in.): 4.31  
Ctn Weight (Lbs.): 7.13  
UPC Number: 050169354131  
I2of5: 50050169354136