


**45 DEGREE GROUNDING CONDUIT AND CORD CONNECTORS****45° Insulated Connector with Ground Lug, Steel/Malleable Iron**
N/A**B51**

Catalog #: 3561-3

APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit, when installation of a copper or aluminum external bonding jumper is required
RACO grounding liquidtight connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
All metallic components are zinc electro plated for added corrosion protection
Malleable Iron castings mate with other components perfectly without strain or distortion
3/8 in. to 2 in. Malleable iron bodies
3/8 in. to 1 in Steel nuts, 1-1/4 in. to 2 in. Malleable iron nuts
N/A

UL LISTED

Standard 514B, UL Listed E195969

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 3/8 in.

DRAWING DIMENSIONS

Dimension A: 1-1/16 in.
Dimension B: 17/32 in.
Thread Spec. B: 1/2 in. - 4 NPT
Dimension C: 1-3/8 in.
Dimension D: 1-1/32 in.
Dimension E: 25/32 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 25
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 28.20
Ship Carton Length (in.): 10.00
Ship Carton Width (in.): 5.25
Ship Carton Height (in.): 4.31
Ctn Weight (Lbs.): 7.05
UPC Number: 050169356135
I2of5: 50050169356130