



LOW VOLTAGE EMERGENCY REMOTE TEST BUTTON

EMERGENCY LIGHTING CONTROLS

FEATURES

- Attractive Flush mount design
- Stainless Steel Latching button
- Optional illuminated pilot button
- Low Voltage 24VDC
- Wall plate factory labeled
- Compatible for use with select HCS Emergency controls:
ALCR1277 and NXRC-UL924-UNV*

*ALCR1277 only compatible with Non-Pilot version / NXRC-UL924-UNV only compatible with Pilot Light version



LVS-ERTB-PL-WH



LVS-ERTB-NP-WH



RELATED PRODUCTS

[UL924 Automatic Load Relay](#)

[NX UL924 Room Controller](#)

SPECIFICATIONS

CONSTRUCTION

- High impact polycarbonate cover plate, stainless steel button switch
- Available only in white
- 3.15"W x 4.94"H x .25"D
- 2.9 oz (82g)

MOUNTING

- Mounts to standard single-gang switch box, Raco 500 series or equivalent

ELECTRICAL

- Class 2 Low Voltage 24 VDC
- 3 Amp Maximum current

OPERATION

- Rated for Indoor Use Only
- Operating Temperature: -4° to 131°F (-20° to 55°C)
- Relative humidity (non-condensing): 0 to 95%

CERTIFICATIONS

- UL
- IP67

WARRANTY

- 5 year limited
- See [Hubbell Control Solutions Standard Warranty](#) for additional information

ORDERING GUIDE

Example: LVS-ERTB-PL-WH

CATALOG #

LVS			
Model	Button Type	Pilot Light	Color
LVS Low Voltage	ERTB Emergency Remote Test Button	PL Pilot Light ¹ NP Non-Pilot Light ²	WH White

Notes:

- NXRC-UL924-UNV only compatible with Pilot Version (PL)
- ALCR1277 only compatible with Non-Pilot Version (NP)

