



* Representative image

Veri*Lite Line Post Insulator SR 46 kV

by OHIO BRASS
Catalog ID: 80S0460F09

Vertical Line Post 46 kV F-Neck / Stud Base 3/4"-10 Tap.

Product Details

General

Application	Vertical Line Post
Cantilever Bending Strength - Max.	2800 Lbs (12.5 kN)
Cantilever Bending Strength - Routine	1235 Lbs. (5.5 kN)
Fitting - Ground/Base	3/4" Stud Base
Fitting - Live Line End	F-Neck
Material	Silicone
Material - End Fitting	Galvanized Steel
Number of Sheds	8
Tension Range	2500 lb
UPC	096359402435

Dimensions

Angle	0
Diameter - Shed(s)	7.1" (179mm) / 4.4" (112mm)
Length - Effective	19.5 in
Rod Diameter	1.75 in
Thickness - Housing	0.15" (3.8mm)
Weight	13.9 lb

Electrical Ratings

Arc Distance - Dry	14.4" (390mm)
Creep and Leakage Distance	34.3" (872mm)
Critical Impulse Flashover (CIFO) - Positive	260 kV
Flashover Voltage - 60 Hz Dry	170 kV

Flashover Voltage - 60 Hz Wet	125 kV
Voltage - Line	46000 V
Voltage Rating	46 kV
Withstand Voltage - Lightning Impulse (Positive)	235 kV

Certifications and Compliance

Industry Standard(s)	ANSI
----------------------	------

Logistics

Pallet Quantity	35 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com