



# Compression Deadend

by FARGO  
Catalog ID: 861022

Compression Deadend, Static Wire, No Jumper Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.306 - 0.312



\* Representative image

## Product Details

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Single Die
Material	Steel
Material - Body	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pad	Cast Aluminum
Number of Pad Holes	0
Press Minimum	12 to
Product Category	Steel
Style	Static Wire, No Jumper Pad
Tension Range	0 lb
Type	Compression
UPC	096359251705

### Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in

Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	10.6 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	1.960 lb

#### Conductor Related

Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter - Maximum	0.312 in
Conductor Diameter - Minimum	0.306 in
Conductor Diameter Range	0.306 - 0.312
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

**For further technical assistance, please contact us**

#### **Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### **International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)