



# Compression Deadend

by FARGO  
Catalog ID: 8614305

Compression Deadend, Static Wire, 2-hole Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.417 - 0.435



\* Representative image

## Product Details

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Single Die
Material	Steel
Material - Body	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pad	Cast Aluminum
Number of Bolt Holes	2
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Steel
Style	Static Wire, 2-hole Pad
Tension Range	0 lb
Type	Compression
UPC	096359270737

### Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in

Diameter - Inside	0 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	13.4 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	0.980 lb

### Conductor Related

Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter - Maximum	0.435 in
Conductor Diameter - Minimum	0.417 in
Conductor Diameter Range	0.417 - 0.435
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)