

* Representative image

Terminal, Aluminum Compression

by ANDERSON
Catalog ID: ACF475B

Terminal, Aluminum Compression, Cable to 2-hole Flat, cable range 0.743-0.814. TERMINAL, AL COMP 0.743-0.814 IN, B PAD

- 90° pad orientation available, 45° pad orientation available

Product Details

General

Material	Aluminum
Number of Bolt Holes	2
Number of Ground Braid Lug Holes	0
Number of Pad Holes	2
Type	Terminal, Cable to Flat
UPC	096359279563

Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	0.882 lb
Width - Pad	1.5 in

Electrical Ratings

Maximum Current Rating Amps Continuous	0

Conductor Related

Conductor Compatibility	ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37
Conductor Diameter - Maximum	0.814 in

Conductor Diameter - Minimum	0.743 in
Conductor Diameter Range	0.743 - 0.814
Conductor Type	• AAC • ACSR

For further technical assistance, please contact us

Domestic Customer Service
Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service
Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com