



Industrial Control Transformer 1KVA 208-600 - 85-130 F2

By Acme Electric
Catalog # CE1000N007CF2

ICT 1KVA 208-600 - 85-130 F2



Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

General

Application Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Color Black
Secondary Voltage 85-130 V
UPC 047503015117

Dimensions

| | |
|------------|-------------------------|
| Dimensions | 7.62 in x 7 in x 6.9 in |
| Height | 6.9 in |
| Length | 7.62 in |
| Weight | 30 lb |
| Width | 7 in |

Electrical Ratings

| | |
|-----------------|-----------|
| Primary Voltage | 208/600 V |
|-----------------|-----------|

Certifications And Compliance

| | |
|------------------|------------|
| Certified Listed | UL Listed |
| | cUL Listed |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 1 |
| Pallet Quantity | 24 |

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-CE1000N007CF2-SPEC-EN | REV 6/2024