



\* Representative image

# Protecta\*Lite Arrester (48 kV MCOV)

by OHIO BRASS  
Catalog ID: 605048F6N0001

This web listing represents a sampling of typical configurations. ProtectaLite Arrester assemblies can be customized for all distribution and transmission lines. Selection of arrester MCOV size is based upon the maximum continuous voltage that is applied across the arrester in service (line-to-ground). For arresters on effectively grounded neutral systems, this is normally the maximum line-to-ground voltage. Example: 84 kV on a 138 kV system. For ungrounded or impedance-grounded systems, the MCOV should be at least 90 percent of maximum phase-to-phase voltage. For more information about arrester selection, please contact your Hubbell Power Systems representative.

- To learn more about how Protecta\*Lite improves line performance, click here to visit our blog.

## Product Details

### General

Application	Above 35 kV
Type	Line Arresters
UPC	096359437574

### Electrical Ratings

Creep and Leakage Distance	92.4 in (2347.0 mm)
Duty Cycle	60 kV
Frequency Rating	48-62 Hz
MCOV	48 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	170.4 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 135.6 kV @ 1.5 kA</li> <li>• 142.8 kV @ 3 kA</li> <li>• 149.4 kV @ 5 kA</li> <li>• 161.4 kV @ 10 kA</li> <li>• 178.8 kV @ 20 kA</li> <li>• 201 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	126.6 kV
Pressure Relief Capability-Symmetrical rms (kA)	40
Voltage - Line	69 kV

### Certifications and Compliance

Industry Standard(s)	IEEE/IEC
----------------------	----------

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com

