



* Representative image

Protecta*Lite Arrester (15.3 kV MCOV)

by OHIO BRASS
Catalog ID: 612015G1G0001

This web listing represents a sampling of typical configurations. ProtectaLite Arrester assemblies can be customized for all distribution and transmission lines. Selection of arrester MCOV size is based upon the maximum continuous voltage that is applied across the arrester in service (line-to-ground). For arresters on effectively grounded neutral systems, this is normally the maximum line-to-ground voltage. Example: 84 kV on a 138 kV system. For ungrounded or impedance-grounded systems, the MCOV should be at least 90 percent of maximum phase-to-phase voltage. For more information about arrester selection, please contact your Hubbell Power Systems representative.

- To learn more about how Protecta*Lite improves line performance, click here to visit our blog.

Product Details

General

Application	35 kV and Below
Type	Line Arresters
UPC	096359455417

Electrical Ratings

Creep and Leakage Distance	25.2 in (640.1 mm)
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	60.6 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 45.4 kV @ 1.5 kA • 48.4 kV @ 3 kA • 51.3 kV @ 5 kA • 56.4 kV @ 10 kA • 63.5 kV @ 20 kA • 75.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	43.5 kV
Pressure Relief Capability-Symmetrical rms (kA)	20
Voltage - Line	23 kV

Certifications and Compliance

Industry Standard(s)	IEEE/IEC
----------------------	----------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com

