



# Industrial Control Transformer .100KVA 208,230,460 -115 F2

By Acme Electric  
Catalog # [CE100N005CF2](#)

TFMR 1PH .100KVA 208,230,460 -115 F2



## Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

## Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

## General

Catalog Number                      CE100N005CF2

Color                                      Black  
Secondary Voltage                      115 V  
UPC                                         047503014387

## Dimensions

Dimensions                                3.69 in x 3.38 in x 4.359 in  
Height                                      4.359 in  
Length                                       3.69 in  
Weight                                       4.2 lb  
Width                                        3.38 in

## Electrical Ratings

Primary Voltage                         208/230/460 V

## Certifications And Compliance

Certified Listed                         

- UL Listed
- cUL Listed

## Logistics

Carton Quantity                         1  
Pallet Quantity                         120

## Product Assets

[Specifications - CE100N005CF2](#)