



# Industrial Control Transformer

## .100KVA 208,277 - 120 F2

By Acme Electric  
Catalog # [CE100N006CF2](#)

ICT .100KVA 208,277 - 120 F2



### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Catalog Number           CE100N006CF2  
Color                         Black

Secondary Voltage           120 V  
UPC                            047503014776

### Dimensions

Dimensions                 3.69 in x 3.38 in x 4.359 in  
Height                       4.359 in  
Length                       3.69 in  
Weight                       4.2 lb  
Width                         3.38 in

### Electrical Ratings

Primary Voltage             208/277 V

### Certifications And Compliance

Certified Listed           

- UL Listed
- cUL Listed

### Logistics

Carton Quantity            1  
Pallet Quantity            120

### Product Assets

[Catalogs - Acme Electric Catalog - Section 5 - Industrial Control Transformers](#)  
[Specifications - CE100N006CF2](#)