


**MULTI GANG RECTANGULAR FLOOR BOXES - CONCRETE POUR****Three-Gang Fully Adjustable Floor Box, Cast Iron
N/A****A99**

Catalog #: 6275

APPLICATIONS

RACO® rectangular series floor boxes are ideally suited for heavy floor traffic applications, such as malls, department stores, banks and schools. Floor boxes are installed in poured concrete floors and are fed with conduit and are used in branch circuit wiring. RACO® multiple-gang rectangular floor box series may be used for both single-service and three-service (power and voice/data) applications.

PRODUCT FEATURES

Cast iron, water-tight body, fully adjustable
Gray powder coat paint inside and out for additional corrosion resistance
Interior and exterior leveling screws permit adjustment to meet finished floor
Removable partitions included to meet larger capacity requirements on two and three gang boxes
Disposable concrete cap to prevent the entry of concrete during pour included
3/4" threaded conduit openings are standard
RACO® 6250, 6288, 6289, or 6291 brass cover must be ordered separately
N/A

UL LISTED

File E195978

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATIONNumber Of Outlets: 8 (Side Only)
Gangs: 3**PRODUCT MEASUREMENTS**Outlet Size: 3/4 in.
Cubic Inches (cm3): 34.8 (570.2) Mid Gang, 36.5 (598.0) End Gang
Wt. Ea. (Lbs.): 10.110
Product Length (in.): 4.13
Product Width (in.): 11.25
Product Height (in.): 3.75**PACKAGING**Minimum Pack Qty.: 4
Std. Pkg.: 4
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 1011.00
Ship Carton Length (in.): 14.20
Ship Carton Width (in.): 4.80
Ship Carton Height (in.): 6.70
Ctn Weight (Lbs.): 40.44
Pallet Qty: 756
UPC Number: 050169062753
I2of5: 50050169062758