



Industrial Control Transformer .100KVA 240X480 - 24 F2

By Acme Electric
Catalog # CE100N013CF2

ICT .100KVA 240X480 - 24 F2



Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

General

Application Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Color Black
 Secondary Voltage 24 V
 UPC 047503016176

Dimensions

Dimensions	3.78 in x 3.38 in x 4.359 in
Height	4.359 in
Length	3.78 in
Weight	4.2 lb
Width	3.38 in

Electrical Ratings

Primary Voltage	240 X 480 V
-----------------	-------------

Certifications And Compliance

Certified Listed	UL Listed
	cUL Listed

Logistics

Carton Quantity	1
Pallet Quantity	120

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-CE100N013CF2-SPEC-EN | REV 6/2024