



# Industrial Control Transformer

## 2KVA 240,480,600 - 100,120 F2

By Acme Electric  
Catalog # CE2000N011CF2

ICT 2KVA 240,480,600 - 100,120 F2



### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Catalog Number CE2000N011CF2

Color Black  
Secondary Voltage 100, 120 V  
UPC 047503015841

### Dimensions

Dimensions 7.98 in x 7 in x 6.68 in  
Height 6.68 in  
Length 7.98 in  
Weight 38 lb  
Width 7 in

### Electrical Ratings

Primary Voltage 240/480/600 V

### Certifications And Compliance

- Certified Listed
- UL Listed
  - cUL Listed

### Logistics

Carton Quantity 1  
Pallet Quantity 24

### Product Assets

[Specifications - CE2000N011CF2](#)