



Compression Deadend

by FARGO
Catalog ID: 861227S

Compression Deadend, Static Wire, 2-hole Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.385 - 0.392



* Representative image

Product Details

General

| | |
|--|-------------------------|
| Bolt Installation Torque (Recommended) | 0 ft-lbs |
| Compression Method | Single Die |
| Material | Steel |
| Material - Body | Galvanized Forged Steel |
| Material - Hardware | Aluminum Alloy |
| Material - Pad | Cast Aluminum |
| Number of Bolt Holes | 2 |
| Number of Pad Holes | 0 |
| Press Minimum | 60 to |
| Product Category | Steel |
| Style | Static Wire, 2-hole Pad |
| Tension Range | 0 lb |
| Type | Compression |
| UPC | 096359270720 |

Dimensions

| | |
|------------------------------------|------|
| Actual Clamp Strand Diameter Range | 0 in |
| Adjustment Step | 0 in |
| Angle - Pad | 0 ° |
| Clamping - Maximum | 0 in |
| Clamping - Minimum | 0 in |
| Diameter - Clamping Hardware | 0 in |
| Diameter - Clevis Pin | 0 in |
| Diameter - Eye Hole | 0 in |

| | |
|---------------------------|----------|
| Diameter - Inside | 0 in |
| Diameter - Pad Bolt | 0 in |
| Length - Pin | 0 in |
| Length Before Compression | 10.6 in |
| Take Up | 0 in |
| Thickness - Pad | 0 in |
| Total Adjustment | 0 in |
| Weight | 1.810 lb |

Conductor Related

| | |
|-------------------------------------|---------------|
| Conductor Diameter (Main) - Maximum | 0 in |
| Conductor Diameter (Main) - Minimum | 0 in |
| Conductor Diameter - Maximum | 0.392 in |
| Conductor Diameter - Minimum | 0.385 in |
| Conductor Diameter Range | 0.385 - 0.392 |
| Messenger Diameter - Maximum | 0 in |
| Messenger Diameter - Minimum | 0 in |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com