



# Compression Deadend

by FARGO  
Catalog ID: 861635S

Compression Deadend, Static Wire, 2-hole Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.486 - 0.495



\* Representative image

## Product Details

### General

|  |                         |
|--|-------------------------|
| Bolt Installation Torque (Recommended) | 0 ft-lbs                |
| Compression Method                     | Single Die              |
| Material                               | Steel                   |
| Material - Body                        | Galvanized Forged Steel |
| Material - Hardware                    | Aluminum Alloy          |
| Material - Pad                         | Cast Aluminum           |
| Number of Bolt Holes                   | 2                       |
| Number of Pad Holes                    | 0                       |
| Press Minimum                          | 60 to                   |
| Product Category                       | Steel                   |
| Style                                  | Static Wire, 2-hole Pad |
| Tension Range                          | 0 lb                    |
| Type                                   | Compression             |
| UPC                                    | 096359270751            |

### Dimensions

|                                    |      |
|------------------------------------|------|
| Actual Clamp Strand Diameter Range | 0 in |
| Adjustment Step                    | 0 in |
| Angle - Pad                        | 0 °  |
| Clamping - Maximum                 | 0 in |
| Clamping - Minimum                 | 0 in |
| Diameter - Clamping Hardware       | 0 in |
| Diameter - Clevis Pin              | 0 in |
| Diameter - Eye Hole                | 0 in |

|                           |          |
|---------------------------|----------|
| Diameter - Inside         | 0 in     |
| Diameter - Pad Bolt       | 0 in     |
| Length - Pin              | 0 in     |
| Length Before Compression | 13.4 in  |
| Take Up                   | 0 in     |
| Thickness - Pad           | 0 in     |
| Total Adjustment          | 0 in     |
| Weight                    | 3.500 lb |

### Conductor Related

|                                     |               |
|-------------------------------------|---------------|
| Conductor Diameter (Main) - Maximum | 0 in          |
| Conductor Diameter (Main) - Minimum | 0 in          |
| Conductor Diameter - Maximum        | 0.495 in      |
| Conductor Diameter - Minimum        | 0.486 in      |
| Conductor Diameter Range            | 0.486 - 0.495 |
| Messenger Diameter - Maximum        | 0 in          |
| Messenger Diameter - Minimum        | 0 in          |

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)