



# Industrial Control Transformer

## .250KVA 240X480-120 F1

By Acme Electric  
Catalog # CE250N008CF1

ICT .250KVA 240X480-120 F1



### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Catalog Number CE250N008CF1

Color Black  
Secondary Voltage 120 V  
UPC 047503015445

### Dimensions

Dimensions 4.547 in x 4.5 in x 5.2897 in  
Height 5.2897 in  
Length 4.547 in  
Weight 10 lb  
Width 4.5 in

### Electrical Ratings

Primary Voltage 240 X 480 V

### Certifications And Compliance

Certified Listed

- UL Listed
- cUL Listed

### Logistics

Carton Quantity 1  
Pallet Quantity 72

### Product Assets

[Specifications - CE250N008CF1](#)