



Compression Deadend

by FARGO
Catalog ID: 861635

Compression Deadend, Static Wire, No Jumper Pad, for EHS Steel, Alumoweld(R), Dia. Range 0.486 - 0.495



* Representative image

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Compression Method	Single Die
Material	Steel
Material - Body	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Pad	Cast Aluminum
Number of Pad Holes	0
Press Minimum	60 to
Product Category	Steel
Style	Static Wire, No Jumper Pad
Tension Range	0 lb
Type	Compression
UPC	096359482796

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in

Diameter - Pad Bolt	0 in
Length - Pin	0 in
Length Before Compression	13.4 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	2.740 lb

Conductor Related

Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter - Maximum	0.495 in
Conductor Diameter - Minimum	0.486 in
Conductor Diameter Range	0.486 - 0.495
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com