




* Representative image

Terminal, Aluminum Compression

by ANDERSON
Catalog ID: ACF350B

Terminal, Aluminum Compression, Cable to 2-hole Flat, cable range 0.618-0.684. TERMINAL, AL COMP 0.618-0.684 IN, B PAD

- 90° pad orientation available, 45° pad orientation available

Product Details

General

Material	Aluminum
Number of Bolt Holes	2
Number of Ground Braid Lug Holes	0
Number of Pad Holes	2
Type	Terminal, Cable to Flat
UPC	096359279402

Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	0.588 lb
Width - Pad	1.5 in

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Compatibility	ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;AAC-Tulip-336.1-19;AAC-Daffodil-350-19
Conductor Diameter - Maximum	0.684 in
Conductor Diameter - Minimum	0.618 in

Conductor Diameter Range	0.618 - 0.684
Conductor Type	• AAC • ACSR

Logistics

Pallet Quantity	3840 EA
-----------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com