



Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 6kVA

By Acme Electric
Catalog # [A3006K0310B](#)

Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 6kVA



*Representative Image

Features

- Copper terminations for trouble free operation
- Lower cost solution
- 5-10 times increase in kVA

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	220/230/240
Product Category	Buck-Boost Transformer
Secondary Voltage	208 V
UL Insulation Class	180°C
UPC	047503092378
Winding Material	AL
kVA	6

Dimensions

Dimensions	7.47 in x 12.37 in x 10.38 in
Height	10.38 in
Length	7.47 in
Weight	75 lb
Width	12.37 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[3D Models - Group_24](#)
[Brochures - 3PhaseBuckBoost](#)
[Brochures - Buck-Boost Transformers](#)
[Catalogs - Acme Electric Catalog - Section 7 - Buck Boost Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Installation Manuals - Manual A-701953-A](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - Product Information Video Series - 3 Phase Buck Boost](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-A3006K0310B-SPEC-EN | REV 1/2024