



# Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 45kVA

By Acme Electric  
Catalog # A3045K0310B

Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 45kVA



\*Representative Image

## Features

- Copper terminations for trouble free operation
- Lower cost solution
- 5-10 times increase in kVA

## General

Catalog Number	A3045K0310B
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	220/230/240
Product Category	Buck-Boost Transformer
Secondary Voltage	208 V
UL Insulation Class	180°C
UPC	047503092415
Winding Material	AL
kVA	45

## Dimensions

Dimensions	7.37 in x 19.25 in x 15.21 in
Height	15.21 in
Length	7.37 in
Weight	156 lb
Width	19.25 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

## Certifications And Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

## Logistics

Carton Quantity	1
Pallet Quantity	10

## Product Assets

- [Brochures - 3 Phase Buck Boost Transformers](#)
- [Brochures - Buck-Boost Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - Product Information Video Series - 3 Phase Buck Boost](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
ACME-A3045K0310B-SPEC-EN | REV 6/2024