



## Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 112.5kVA

By Acme Electric  
Catalog # [A3112K0310B](#)

Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 112.5kVA



\*Representative Image

### Features

- Copper terminations for trouble free operation
- Lower cost solution
- 5-10 times increase in kVA

### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	208 V
UPC	047503006979
Winding Material	AL
kVA	112.5

### Dimensions

Dimensions	11.14 in x 27.13 in x 24.81 in
Height	24.81 in
Length	11.14 in
Weight	600 lb
Width	27.13 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

### Certifications and Compliance

Nema Rating	NEMA 3R
-------------	---------

### Product Assets

- [3D Models - Group\\_55](#)
- [Catalogs - Acme Electric Catalog - Section 7 - Buck Boost Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Installation Manuals - Manual A-701953-A](#)
- [SDS - HCC\\_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - Product Information Video Series - 3 Phase Buck Boost](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-A3112K0310B-SPEC-EN | REV 1/2024