



Industrial Control Transformer .100KVA 240X480-120 F2

By Acme Electric
Catalog # [CE100N008CF2](#)

ICT .100KVA 240X480-120 F2



Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

General

Catalog Number CE100N008CF2

Color Black
Secondary Voltage 120 V
UPC 047503015544

Dimensions

Dimensions 3.778 in x 3.375 in x 4.356 in
Height 4.356 in
Length 3.778 in
Weight 4.2 lb
Width 3.375 in

Electrical Ratings

Primary Voltage 240 X 480 V

Certifications And Compliance

- Certified Listed
- UL Listed
 - cUL Listed

Logistics

Carton Quantity 1
Pallet Quantity 120

Product Assets

[Specifications - CE100N008CF2](#)