



# Industrial Control Transformer

## .500KVA 208,277 - 120 F2

By Acme Electric  
Catalog # CE500N006CF2

ICT .500KVA 208,277 - 120 F2



### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Catalog Number CE500N006CF2

Color Black  
Secondary Voltage 120 V  
UPC 047503014813

### Dimensions

Dimensions 5.17 in x 5.25 in x 5.91 in  
Height 5.91 in  
Length 5.17 in  
Weight 19.2 lb  
Width 5.25 in

### Electrical Ratings

Primary Voltage 208/277 V

### Certifications And Compliance

Certified Listed

- UL Listed
- cUL Listed

### Logistics

Carton Quantity 1  
Pallet Quantity 48

### Product Assets

[Specifications - CE500N006CF2](#)